

3GAA071312-ASE

General Information

Product ID:	3GAA071312-ASE
ABB Type Designation:	M3AA 71B 2
Catalog Description:	No Description Available

Additional Information

ABB Type Designation:	M3AA 71B 2
Altitude:	1000 m
Ambient Temperature:	40 °C
Bearing:	6203-2ZC3
Bearing NDE:	6202-2ZC3
Country of Origin:	Poland (PL) China (CN)
Customs Tariff Number:	85015100
Direction of Rotation:	Both sides

Electrical Data:

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	230 V	0.55 kW	2790 r/min	2.20 A	0.780	78.40 %	1.88 N·m	5.30
Y	--	50 Hz	400 V	0.55 kW	2790 r/min	1.29 A	0.780	78.40 %	1.88 N·m	5.30
Y	--	60 Hz	460 V	0.55 kW	3420 r/min	1.12 A	0.750	81.90 %	1.53 N·m	6.60

Gross Weight:	6.4 kg
IC Class:	IC411
IM Class:	IMB3 IM1001
IP Class:	IP55
Insulation Class:	ICLF
Lubrication:	For life
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Package Level 1 Units:	0 carton
Poles (High):	2
Product Name:	3-Phase squirrel cage motor
Product Net Weight:	5.9 kg
Quote Only:	No
Selling Unit of Measure:	piece
Standards:	IEC_60034-1
Starting of Motor:	Direct Online
Stocked At (Warehouses):	Central Stock Europe Central Stock Nordic CSCNM CSI
Temperature Class Default:	--
Terminator Box Location:	D-End top
Two Speed Motor:	No
Type of Duty:	S1
Voltage Code:	S