


NOTES:

- Unless otherwise specified, tolerances:
 $0 < L \leq 4\text{mm} \pm .10\text{mm}$;
 $4 < L \leq 16\text{mm} \pm .20\text{mm}$;
 $16 < L \leq 64\text{mm} \pm .30\text{mm}$;
Terminal Pitch: $\pm .2\text{mm}$ or must fit True Position Grid.

PROPRIETARY INFORMATION Property of Wurth Electronics Midcom Inc. Duplication and/or distribution by permission only.							
REVISIONS							
REV.	CCO NO.	DRFT	CHKR	SAFETY	MFG	COMP	DATE
6A	119746	SLD	YIX	---	---	QYW	7/11/22



FOR WE-MIDCOM USE ONLY		
WIDTH	.882	ref.
BUILD	.269	ref.
PERIMETER	2.117	ref.


Material Manufacturer	Sumitomo Bakelite Co.
Material Name	Sumikon PM-9630
Material Type	Phenolic Molding Compound
Bobbin Weight	-
L.O.I.	-
C.T.I. (volts)	175 - 249
UL Rating	UL94 V-0
UL Yellow Card No.	E41429
Terminals	Phosphor Bronze C5191
Solder Plating	100% Sn (matte)

Supplier must supply a signed & dated Certificate of Conformance, or a packing slip stating material grade, Recognized Company's name & address and quantity shipped, to be kept on file by Midcom QA. C of C must state component is RoSH compliant.

QA Terminals must be solderable per 999-2503.

QA Q.A. to inspect indicated dimensions at incoming inspection.

DRAFTER	S. Durham	7/11/22	MANUFACTURING ENGINEER
CHECKER	Z. Xiang	8/4/22	COMPONENT ENGINEER
This drawing is dual dimensioned Dimensions in brackets are in millimeters.			C. Wang 8/4/22
TOLERANCES UNLESS OTHERWISE SPECIFIED:			SAFETY
Angles: $\pm 1^\circ$ Decimals:			
Fractions: $\pm 1/64$			

DRAWING TITLE		 www.we-online.com/midcom		REV. SEE TABLE ABOVE
BOBBIN PQ3535		DRAWING NO. 070-7331		
SCALE 1:1	SHEET 1 OF 1			