



Model Name: DA03-4

Customer:

Test Mode: HORIZONTAL

Input Voltage: 115Vac

Test Condition: CISPR CLASS-B

Remark: Charging

Test Site: RADIATION

Tested by:

Temp./Hum.:


Output Load: 5V1.5A / Battery / he

RBW:120 KHz VBW:300 KHz

Data: 815

File: D:\DQA_Data\RD\RD_213.EM6 (815)

Date: 2019-03-08 Time: 09:59:37



No.	Freq MHz	Read dBuV	Emission		Limit dBuV	Margin dB	a/pos height	t/pos deg	Remark
			Factor dBuV	Level dBuV					
1	73.74	61.28	-16.89	44.39	40.00	4.39	144	199	Peak
2	73.86	61.05	-16.95	44.10	40.00	4.10	144	199	QP
3	75.36	60.65	-17.46	43.19	40.00	3.19	144	183	Peak
4	75.47	51.58	-17.47	34.11	40.00	-5.89	144	183	QP

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss

Approved by

Reviewed by