

2016-02-11 15:22:09.2643: Log Panel Cleared

2016-02-11 15:22:14.0742: Message Received:

0x00 00 50 00 BF 0E 00 00 88 78	0x00 C3 3F 16 A6 00 00 00 00 00
0x65 3F 00 00 03 88 00 00 00 00	0x00 00 00 00 14 00 01 00 14 21
0xDC 01 55 74 00 00 00 00 00 00	0xFF 02 55 74 00 00 00 00 00 00
0xFF 01 30 31 32 33 34 35 36 37	0x38 39 30 31 32 33 34 35 36 37
0x38 39 53 38	

2016-02-11 15:22:14.0742: Receiving: (0x00) - G3 DC DataTransfer.Indication V3

Interface:	Primary
LQI:	53.0 dB
Confirmation:	Indication
RX_Phase:	15
FCH:	0x0x00 C3 3F 16 A6 00 00 00 00
Band Selection:	CENELEC
Protocol:	G3
Power Level:	101
Tone Map:	0x3F 00 00
Resolution:	6 dB
Gain:	0
Modulation:	8PSK
LQI:	53.0 dB
TX Coef:	0x00 00 00 00 00 00
MPDU Payload Length:	20
MPDU:	
0x01 00 14 21 DC 01 55 74 00 00	0x00 00 00 00 FF 02 55 74 00 00
0x00 00 00 00 FF 01 30 31 32 33	0x34 35 36 37 38 39 30 31 32 33
0x34 35 36 37 38 39 53 38	

2016-02-11 15:22:14.0742: Message Sent:

0x00 80 47 00 01 AF A0 C1 24 08	0x00 10 3F 00 00 0B 00 00 00 00
0x00 00 00 00 00 14 00 01 00 14	0x21 DC 01 55 74 00 00 00 00 00
0x00 FF 01 55 74 00 00 00 00 00	0x00 FF 02 30 31 32 33 34 35 36
0x37 38 39 30 31 32 33 34 35 36	0x37 38 39 56 3E

2016-02-11 15:22:14.0742: Sending: (0x00) - G3 DC DataTransfer.Request V1

Interface:	Primary
NSDU Handle:	36
ARQ:	Enabled
QoS:	Standard Priority
Band Selection:	CENELEC
Protocol:	G3
Power Level:	16
Tone Map:	0x3F 00 00
Resolution:	6 dB
Gain:	1
Modulation:	8PSK
TX Coef:	0x00 00 00 00 00 00
COH:	Off
MPDU Payload Length:	20
MPDU:	
0x01 00 14 21 DC 01 55 74 00 00	0x00 00 00 00 FF 01 55 74 00 00
0x00 00 00 00 FF 02 30 31 32 33	0x34 35 36 37 38 39 30 31 32 33
0x34 35 36 37 38 39 56 3E	

2016-02-11 15:22:14.1542: Message Received:

0x00 10 08 00 CA CA 00 00 24 80	0x00 00
---------------------------------	---------

2016-02-11 15:22:14.1542: Receiving: (0x00) - G3 DataTransfer.Confirmation: - Status= 0000

NSDU Handler:	36
Confirm Flag:	Confirm
Status:	0x0000