


DESIGN:	DATED:	BMS			
CHECKED:	DATED:	CODE:	REL:	DRAWING NO:	REV:
QUALITY CONTROL:	DATED:	E	REVISION		
BILLAMET:	DATED:				
		SCALE: <Scale>		SHEET: 8 9	

CCM Mode (NOT HICCUP MODE)



Parameter	Symbol	Min	Typ	Max	Unit
Common-mode input voltage	V_{CM}	-0.3	12	26	V
Supply Voltage	V_S	2.2	5	26	V
Ambient Temperature	T_A	-40		125	$^{\circ}\text{C}$