



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C): 1-4 (tie 2+3) , 0.059 Ohms $\pm 20\%$.

5-6 , 0.455 Ohms $\pm 20\%$.

12-7 , 0.025 Ohms $\pm 20\%$.

11-8 , 0.025 Ohms $\pm 20\%$.

DIELECTRIC RATING: 1500VAC, 1 minute tested by applying 1875VAC for 1 second between pins 1-12(tie 2+3, 4+5, 11+12).

INDUCTANCE: 190 μ H min., 100kHz, 100mVAC, 0mADC, 1-4(tie 2+3), Ls.

LEAKAGE INDUCTANCE: 2 μ H max., 100kHz, 100mVAC, 1-4(tie 2+3, 7+8+11+12), Ls.

URNS RATIO: (1-4):(5-6) , (1):(1.00), tie(2+3), $\pm 2\%$.

(1-4):(12-7) , (3.5):(1.00), tie(2+3), $\pm 2\%$.

(1-4):(11-8) , (3.5):(1.00), tie(2+3), $\pm 2\%$.

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ (.127mm)		WE-Midcom, Inc.	
	Drawing Title Transformer		Drawing Number 750311492	Rev. 01
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1 Engineer: EJK		Scale ----	Sheet 2 of 5 01/08/2010