



Model Name: DA03-4

Customer:

Test Mode: VERTICAL

Input Voltage: 115Vac

Test Condition: CISPR CLASS-B

Remark: Charging

Test Site: RADIATION

Tested by:

Temp./Hum.:


Output Load: 5V1.5A / Battery / he

RBW:120 KHz VBW:300 KHz

Data: 818

File: D:\DQA_Data\RD\RD_213.EM6 (818)

Date: 2019-03-08 Time: 10:04:10



No.	Freq MHz	Read dBuV	Emission		Limit dBuV	Margin dB	a/pos height	t/pos deg	Remark
			Factor dBuV	Level dBuV					
1	73.74	63.45	-19.88	43.57	40.00	3.57	144	292	Peak
2	73.85	61.69	-19.87	41.82	40.00	1.82	144	292	QP

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss

Approved by

Reviewed by