



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect




TERM. NO.'s FOR REF. ONLY




DOT LOCATES TERM. #1

LOT CODE & DATE CODE



CUSTOMER TO DETERMINE LAND LAYOUT



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	ohms max.
D.C. RESISTANCE	8-6 @20°C	ohms max.
INDUCTANCE	2-4 10kHz, 100mV, Ls	100µH ±10%
SATURATION CURRENT	2-4 20% rolloff from initial	3A
LEAKAGE INDUCTANCE	2-4 tie(6+8),100kHz, 100mV, Ls	µH max.
DIELECTRIC	2-8 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(2-4):(8-6)	2.46:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Preliminary

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13] This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	DRAWING TITLE INDUCTOR	PART NO. 750344515
DATE	Method: Tape & Reel				
ENG	TLI				
REV.	00				
DATE	2019/9/11	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1