

QL0200I-A



PERFORMANCE

- Lithium ion rechargeable cell
- High power design

CHEMISTRY

- LNCAO

MAIN APPLICATIONS

- Medical implants
- Sensors

KEY FEATURES

- Zero-Volt™ enabled
- Implantable
- Highly reliable
- Domestically produced
- UL1642 certified
- Biocompatibility
- Low self discharge/long calendar life at elevated temperature
- Extended cycle life
- Compact and light weight
- Hermetically sealed

SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

Nominal Capacity	200 mAh
Nominal Voltage	3.6 V
Maximum Recommended Continuous Discharge Current	200 mA
Operating Discharge Temperature	32°C to 42°C

PHYSICAL CHARACTERISTICS

Width	17 mm
Height	35 mm
Thickness	5.5 mm
Weight	8 g
Volume	3.27 cc

FOR MORE INFORMATION

Contact Paul Beach
paulb@quallion.com
818.833.2000

www.quallion.com

