



Measurement: Gain / Phase



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	343.107 kHz	118.326 kHz	-224.781 kHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	0 dB	11.641 dB	11.641 dB
Trace 2	Phase (°)	Phase (°)	Phase (°)
Measurement	74.775 °	65.079 °	-9.696 °

Sweep	
Start frequency:	100 Hz
Stop frequency:	1 MHz
Center frequency:	500.05 kHz
Span:	999.9 kHz
Sweep mode:	Logarithmic
Numer of points:	201

Calibration	Full-Range	User-Range
Gain	-	-
Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ
Attenuator setting	Channel 1	Channel 2
Transmission	20 dB	20 dB

Measurement: Gain / Phase



Hardware setup

Device type:	No device connected!
Serial number:	No device connected!
Receiver bandwidth:	30 Hz
Reference level	0 dBm
DUT settling time:	0 s