



Model Name: DA03-4

Customer:

Test Mode: HORIZONTAL

Input Voltage: 230Vac

Test Condition: CISPR CLASS-B

Remark: Charging

Test Site: RADIATION

Tested by:

Temp./Hum.:


Output Load: 5V1.5A / Battery / No

RBW:120 KHz VBW:300 KHz

Data: 812

File: D:\DQA_Data\RD\RD_213.EM6 (812)

Date: 2019-03-08 Time: 09:53:55



No.	Freq MHz	Read dBuV	Emission		Limit dBuV	Margin dB	a/pos height	t/pos deg	Remark
			Factor dBuV	Level dBuV					
1	73.74	61.27	-16.89	44.38	40.00	4.38	144	194	Peak
2	73.86	60.11	-16.94	43.17	40.00	3.17	144	194	QP
3	75.36	59.33	-17.46	41.87	40.00	1.87	144	220	Peak
4	75.48	54.28	-17.47	36.81	40.00	-3.19	144	220	QP

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss

Approved by

Reviewed by