


Test Report



Final Result

Frequency (MHz)	QuasiPeak (dB μ V/m)	Limit (dB μ V/m)	Margin (dB)	Meas. Time (ms)	Bandwidth (kHz)	Height (cm)	Pol	Azimuth (deg)	Corr. (dB/m)
34.506474	40.47	40.00	-0.47	1000.0	120.000	100.0	V	351.0	11.8
39.724442	36.05	40.00	3.95	1000.0	120.000	100.0	V	236.0	13.8

(continuation of the "Final_Result" table from column 16 ...)

Frequency (MHz)	Comment
34.506474	22:49:18 - 13-09-2024
39.724442	22:58:48 - 13-09-2024

Critical Freqs

Frequency (MHz)	MaxPeak (dB μ V/m)	Limit (dB μ V/m)	Margin (dB)	Meas. Time (ms)	Bandwidth (kHz)	Height (cm)	Pol	Azimuth (deg)	Corr. (dB/m)
30.025526	38.68	40.00	1.32	---	---	100.0	V	225.0	11.0
34.506474	40.50	40.00	-0.50	---	---	100.0	V	350.0	12.1
35.130790	41.01	40.00	-1.01	---	---	100.0	V	0.0	12.1
39.724442	35.58	40.00	4.42	---	---	100.0	V	235.0	13.6
68.238421	36.51	40.00	3.49	---	---	100.0	V	270.0	11.2
69.438158	37.49	40.00	2.51	---	---	100.0	V	270.0	10.7
124.983421	38.48	40.00	1.52	---	---	100.0	V	315.0	10.3
174.989474	32.95	40.00	7.05	---	---	300.0	H	90.0	10.3
199.979737	34.20	40.00	5.80	---	---	200.0	H	135.0	12.7

(continuation of the "Critical_Freqs" table from column 16 ...)

Frequency (MHz)	Comment
30.025526	23:02:47 - 13-09-2024
34.506474	22:49:07 - 13-09-2024
35.130790	23:02:44 - 13-09-2024
39.724442	22:57:38 - 13-09-2024
68.238421	23:02:53 - 13-09-2024
69.438158	23:02:50 - 13-09-2024
124.983421	23:04:21 - 13-09-2024
174.989474	23:04:39 - 13-09-2024
199.979737	23:04:45 - 13-09-2024