




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE 4-1	@20°C	0.500 ohms ±10%
D.C. RESISTANCE 3-5	@20°C	0.125 ohms ±10%
D.C. RESISTANCE 6-10	@20°C	0.040 ohms ±20%
INDUCTANCE 4-1	10kHz, 100mV, Ls	350µH ±10%
LEAKAGE INDUCTANCE 4-1	tie(3+5, 6+10), 100kHz, 100mV, Ls	µH typ., µH max.
DIELECTRIC 1-10	tie(4+5), 3750VAC, 1 second	3000VAC, 1 minute
DIELECTRIC 10-Core	3750VAC, 1 second	3000VAC, 1 second
URNS RATIO	(4-2):(2-1)	1:1, ±1%
URNS RATIO	(4-1):(5-3)	4.67:1, ±1%
URNS RATIO	(4-1):(10-6)	7:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.