

more than you expect

WE

WÜRTH ELEKTRONIK

* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



	PARAMETER		TEST CONDITIONS	VALUE
⑥③	D.C. RESISTANCE	1-2	②20°C	3.5 ohms ±10%
⑥③	D.C. RESISTANCE	2-3	②20°C	2.6 ohms ±10%
⑥③	D.C. RESISTANCE	5-6	②20°C	0.048 ohms ±20%
⑥③	D.C. RESISTANCE	7-8	②20°C	0.387 ohms ±10%
⑥③	INDUCTANCE	1-3	10kHz, 100mVAC, Ls	9.94mH ±10%
	LEAKAGE INDUCTANCE	1-3	tie(5+6, 7+8), 100kHz, 100mVAC, Ls	180.0uH max.
	DIELECTRIC	2-6	2500VAC, 1 second	2000VAC, 1 minute
	DIELECTRIC	6-8	2500VAC, 1 second	2000VAC, 1 minute
	URNS RATIO		(2-3):(1-2)	1:1, ±1%
⑥③	URNS RATIO		(1-3):(6-5)	21:1, ±1%
⑥③	URNS RATIO		(1-3):(8-7)	17.29:1, ±1%



REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750310334
6E	1/10	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750310334 	SPECIFICATION SHEET 1 OF 1
6D	7/09	PKG-0690				
6C	11/08	www.midcom-inc.com				
6B	9/08	SEE REVISION SHEET FOR REVISION LEVEL				