

更改 REV	变更内容 MODIFICATION	日期 DATE	制图 DRAW	批准 APPROVE
A	图面发行	2012/10/29	JDL	Oscar

NOTES:

MATERIAL:



- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(U194V-0).
2.CONTACT MATERIAL :PHOSPHOR BRONZE Ø0.46mm (C5100).
3.PLATING :GOLD PLATING OVER NICKEL.
4.SHIELD COPPER ALLOY(OR STEEL ALLOY) 0.20mm THICKNESS PLATING NI.
5.LED,OPTION.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
2.CURRENT RATING :1.5 AMP.
3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.

MECHANICAL:

- 1.DURABILITY:750 CYCLES MIN.
2.PCB RETENTION PRE-SOLDER
ENVIRONMENTAL:
1.STORAGE : -40°C TO +85°C.
2. OPERATION: -20°C TO 70°C.
MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.



GREEN



YELLOW



单色灯脚位图

PART NUMBER: 56A-S1188L1-E2XX

GOLD PLATING "U"
1-Fin" 2-2u" 3-3u" 4-6u"
PLASTIC MATERIAL&COLOR:Black/Yellow/Gray
2-PMMA Black

PC Board Layout

◎ :Inspection Item																													
◎ :Cp/Cpk and SPC Control Item																													
					TOLERANCE UNLESS OTHERWISE SPECIFIED																								
.X± 0.20					X°± 1°																								
.XX± 0.15					.X°± 0.5°																								
.XXX± 0.075																													
批准 APPROVE					检查 CHECK																								
图面 DRAWING					图号 FILE NO.					图号 DWG NO.																			
Oscar					PROM										图号 SHEET					1					1				
SCALE					1:1					图号 SIZE					A3					图号 REV					A				