




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-2 @20°C	0.145 ohms ±10%
D.C. RESISTANCE	9-12 @20°C	0.320 ohms ±10%
INDUCTANCE	3-2 10kHz, 100mV, Ls	400µH ±10%
SATURATION CURRENT	3-2 10% rolloff from initial	8.5A
DIELECTRIC	3-12 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-2):(9-12)	8:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

UL Recognized Insulation system M1-130(B), E106391

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750315726
DATE	9/30/2015	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	KLM	PKG-0598				
REV.	00					
DATE	10/7/2015	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1