

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes


more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-1 @20°C	0.035 ohms max.
D.C. RESISTANCE	8-7 @20°C	0.220 ohms max.
D.C. RESISTANCE	6-5 @20°C	0.250 ohms max.
INDUCTANCE	4-1 10kHz, 100mV, Ls	4.5µH ±25%
LEAKAGE INDUCTANCE	4-1 tie(5+6+7+8), 100kHz, 100mV, Ls	150nH max.
DIELECTRIC	1-8 tie(6+7), 1500VAC, 1 second	
TURNS RATIO	(8-7):(4-1)	3:1
TURNS RATIO	(8-7):(6-5)	1:1

* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking detail font and color may vary on preproduction samples.

DFM	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE	PART NO.
DATE	Method: Tape & Reel				
ENG	TLI	PKG-0410			
REV.	00				
DATE	2020/8/18	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1