



$V_{in} = 210 \text{ to } 310\text{V}$
 $V_{start} = 210\text{V}$
 $V_{stop} = 190\text{V}$
 $V_{out} = 12\text{V at } 10\text{A}$
 $F_r = 134\text{kHz}$
 $F_s = 93.4 \text{ to } 147.4\text{kHz}$
 $L_n = 7$
 $Q_e = 0.28$
 $SS = 53.7\text{ms}$

SATCOM DIRECT AVIONICS KANATA, ON, CANADA, K2K 0A1		SD avionics	
SIZE	CAGE CODE	DWG NO.	REV
B	L7359	780-00206	2
SCALE:	1:1 +12V	LLC_Controller_and_Power_Stage.SchDoc	SHEET 8 OF 15