

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes



more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:


PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	ohms max.
D.C. RESISTANCE	8-6 @20°C	ohms max.
INDUCTANCE	2-4 10kHz, 100mV, Ls	100µH ±10%
SATURATION CURRENT	2-4 20% rolloff from initial	3A
LEAKAGE INDUCTANCE	2-4 tie(6+8),100kHz, 100mV, Ls	µH max.
DIELECTRIC	2-8 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(2-4):(8-6)	4:1, ±2%

TERM. NO.'s FOR REF. ONLY



DOT LOCATES TERM. #1

LOT CODE & DATE CODE




CUSTOMER TO DETERMINE LAND LAYOUT

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Rated current: 1.25A



Aux
12V - 0.1A

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications Method: Tape & Reel PKG-1053	 CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE INDUCTOR	PART NO. 750344515
DATE				Angles: ±1° Decimals: ±.005 [.13]		
ENG	TLI			Fractions: ±1/64 Footprint: ± .005 [.13]		
REV.	00			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
DATE	2019/9/16	www.we-online.com/midcom	SPECIFICATION SHEET 1 OF 1			