




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.088 ohms ±20%
D.C. RESISTANCE	3-4 @20°C	0.056 ohms ±20%
D.C. RESISTANCE	6-7 @20°C	0.016 ohms ±20%
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	82.00uH ±10%
SATURATION CURRENT	1-2 20% rolloff from initial	2.7A
LEAKAGE INDUCTANCE	1-2 tie(3+4, 6+7), 100kHz, 100mVAC, Ls	0.6uH typ., 1.2uH max.
DIELECTRIC	1-7 tie(2+3), 1500VAC, 1 second	-
DIELECTRIC	1-4 625VAC, 1 second	-
TURNS RATIO	(2-1):(3-4)	3.33:1, ±1%
TURNS RATIO	(2-1):(6-7)	2.5:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0530 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750317123
6B	4/18			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750317123	
6A	3/18	SEE REVISION SHEET FOR REVISION LEVEL				SPECIFICATION SHEET 1 OF 1