



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-2 @20°C	0.034 ohms ±20%
D.C. RESISTANCE	7-8 @20°C	0.080 ohms ±10%
D.C. RESISTANCE	8-9 @20°C	0.035 ohms ±20%
INDUCTANCE	4-2 10kHz, 100mV, Ls	25.0μH ±10%
SATURATION CURRENT	4-2 20% rolloff from initial	2.2A
LEAKAGE INDUCTANCE	4-2 tie(7+8+9),100kHz, 10mV, Ls	190nH typ., 400nH max.
DIELECTRIC	2-9 2500VDC, 1 second	2500VDC, 1 minute
URNS RATIO	(4-2):(7-8)	1:1, ±1%
URNS RATIO	(4-2):(8-9)	2.8:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750317313
DATE	11/10/2017	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	KLM	PKG-1102				
REV.	00					
DATE	11/14/2017	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1