




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



Update views and footprint to remove terminal #2



**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.055 ohms ±20%
D.C. RESISTANCE	4-5 @20°C	0.235 ohms ±10%
D.C. RESISTANCE	7-8 @20°C	0.235 ohms ±10%
D.C. RESISTANCE	9-10 @20°C	0.180 ohms ±10%
D.C. RESISTANCE	11-12 @20°C	0.180 ohms ±10%
D.C. RESISTANCE	13-14 @20°C	0.180 ohms ±10%
D.C. RESISTANCE	15-16 @20°C	0.180 ohms ±10%
INDUCTANCE	1-3 10kHz, 100mV, Ls	40.00µH ±10%
SATURATION CURRENT	1-3 20% rolloff from initial	TBDA
LEAKAGE INDUCTANCE	1-3 tie(4+5+7+8+1+10+11+12+13+14+15+16), 100kHz, 100mV, Ls	nH typ., TBDnH max.
DIELECTRIC	3-16 tie(1+5+7, 15+14+12+9), 625VAC, 1 second	
DIELECTRIC	16-14 tie(10+11+12+13), 500VAC, 1 second	
DIELECTRIC	13-12 tie(9+14+15), 500VAC, 1 second	
DIELECTRIC	11-10 tie(12+13+15), 500VAC, 1 second	
DIELECTRIC	3-5 500VAC, 1 second	
DIELECTRIC	3-8 500VAC, 1 second	
URNS RATIO	(3-1):(9-10)	1:1, ±1%
URNS RATIO	(3-1):(11-12)	1:1, ±1%
URNS RATIO	(3-1):(13-14)	1:1, ±1%
URNS RATIO	(3-1):(15-16)	1:1, ±1%
URNS RATIO	(3-1):(5-4)	1:1, ±1%
URNS RATIO	(3-1):(8-7)	1:1, ±1%

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Product contains reportable levels of REACH SVHC component Dechlorane Plus™ found in AM113 plastic

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
DATE	Method: Tape & Reel		Angles: ±1°		
ENG	PLP	PKG-0325	Fractions: ±1/64	TRANSFORMER	750318836
REV.	00		Footprint: ±.005 [.13]		
DATE	11/5/2019	www.we-online.com/midcom	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		SPECIFICATION SHEET 1 OF 1