


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	15-16 @20°C	0.115 ohms max.
D.C. RESISTANCE	1-3 tie(1+2,3+4), @20°C	4 mohms max.
D.C. RESISTANCE	5-7 tie(5+6,7+8), @20°C	4 mohms max.
D.C. RESISTANCE	11-13 @20°C	50 mohms max.
INDUCTANCE	11-13 50kHz, 100mV, Ls	280.00µH ±10%
LEAKAGE INDUCTANCE	11-13 tie(1+2+3+4+5+6+7+8), 82kHz, 100mV, Ls	43µH ±10%
DIELECTRIC	15-1 tie(15+11), 3750VAC, 1 second	
URNS RATIO	(11-13):(1,2-3,4)	8.33:1, ±2%
URNS RATIO	(11-13):(5,6-7,8)	8.33:1, ±2%
URNS RATIO	(11-13):(16-15)	12.5:1, ±2%



TERM. NO.'s FOR REF. ONLY
 .114 MIN. [2.90]
 1.110 Max. [28.19]
 DOT LOCATES TERM. #1
 1.890 MAX. [48.00]
 1.811 MAX. [46.00]
 750343657
 LOT CODE & DATE CODE
 PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



SEC
 24 V - 20 A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1,

EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications		 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]		DRAWING TITLE TRANSFORMER	PART NO. 750343657
DATE		Method: Tray			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.			
ENG SLC		PKG-1047						
REV. 01								
DATE 10/20/2017		www.we-online.com/midcom						SPECIFICATION SHEET 1 OF 1

SPECIFICATION SHEET 1 OF 1