


Table 8-2. Switching Frequency Options

Resistor at FSEL (1%)	Switching Frequency
6.2 k Ω to GND	1.5 MHz
Short to GND	2.25 MHz
Short to V_{IN}	2.5 MHz
47 k Ω to V_{IN}	3 MHz

Table 8-5. Default Output Voltage Setpoints

VSEL Pin ¹	VSET[7:0]	I2C Device Address	Output Voltage Setpoint
6.2 k Ω to GND	0x50	0x44	800 mV
Short-Circuit to GND	0x46	0x45	750 mV
Short-Circuit to V_{IN}	0x5F	0x46	875 mV
47 k Ω to V_{IN}	0x24	0x47	580 mV

AEC Lynx-800G		
Title	05 Regulators	
Size B	Document Number <Doc>	Rev A
Date:	Monday, February 10, 2025	Sheet 5 of 7