


Measurement: Gain / Phase



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	1.966 kHz	112.085 kHz	110.119 kHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	0 dB	-24.393 dB	-24.393 dB
Trace 2	Phase (°)	Phase (°)	Phase (°)
Measurement	80.149 °	0 °	-80.149 °

Sweep	
Start frequency:	500 Hz
Stop frequency:	300 kHz
Center frequency:	150.25 kHz
Span:	299.5 kHz
Sweep mode:	Logarithmic
Numer of points:	201

Hardware setup	
Device type:	Bode100R1
Serial number:	MF590C
Receiver bandwidth:	30 Hz
Output level:	-15 dBm
DUT settling time:	0 ms

Calibration	Full-Range	User-Range
Gain	-	-
Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ
Attenuator setting	Channel 1	Channel 2
Transmission	20 dB	20 dB