

APPROVED	CHECKED	CHECKED	CHECKED	FILLED

PAGE :	1/3
DEPT. :	ENGINEERING
DATE :	29/8/2023
REF. NO :	E1MEC- 2380060

ENGINEERING STUDY / ANALYSIS REPORT

SUBJECT : NOISE AND DC LEVEL FOR DCDC IC MC33063ADR PCN

PURPOSE : STUDY NOISE AND DC LEVEL FOR DCDC IC MC33063ADR PCN# 20230417002.1
(Qualification of new Fab site (RFAB) using qualified Process Technology and Die)

MODEL NAME : 8AC22CX1
PART NO. :
SUPPLIER / MAKER :
STUDY STAGE : EVT / DVT / PVT / 1ST LOT / OTHERS:
SAMPLE STAGE : 1ST / 2ND / 3RD SAMPLE / OTHERS:
CHANGE DCDC IC MC33063ADR PCN# 20230417002.1

1. TEST PROCEDURES (CONTENTS) :

1.1 TEST CONDITIONS / ENVIRONMENTS :			
AC Supply :	230	V	Frequency : 50 Hz
DC Supply :		V	
Room Temp.:	25	°C	Room Humidity: 52 %
Test Location:	ENGINEERING STUDY ROOM		
Input Source (Test Signal):	PLAYBACK SONG		Function Mode: USB
Volume Setting:	15	EQ Setting: Flat	Bass / Treble:
Output Level:		V	% THD
Speaker Load / Dummy Impedance :	4		Ohms

1.2 TEST EQUIPMENTS / TOOLS :	
Equipment Name :	EXTECH AC POWER SOURCE
Model No :	6800 SERIES
Serial Number :	
Equipment Name :	YOKOGAWA OSCILLOSCOPE
Model No :	DLM2024
Serial Number :	SR024103
Equipment Name :	
Model No :	
Serial Number :	
Equipment Name :	
Model No :	
Serial Number :	

2.RESULTS / DATA :





2.1 OBSERVATIONS / FINDINGS :
1. Noise level for MC33063ADR PCN# 20230417002.1 increase 40% compare previous MC33063ADR

2.2 ATTACHED DATA / DOCUMENTS : (PLEASE SPECIFY)

3. CONCLUSION :

OK	OK (WITH CONDITION)	NG (NEED IMPROVE)	CAN'T IMPROVE
		O	

REMARKS:

DCDC IC MC33063ADR NOISE**Current DCDC IC MC33063ADR****DCDC IC MC33063ADR PCN# 20230417002.1****DCDC IC MC33063ADR DC LEVEL****Current DCDC IC MC33063ADR****DCDC IC MC33063ADR PCN# 20230417002.1**

Schematic

