







修改SS电容由3.3nF 改成0.1uF
修改OCP电阻由4.3K 改成8.2K
Enable 增加POMS 控制





Vref	0.60V	0.60V	0.60V	0.60V	0.60V	0.60V
RH	10.00K	15.00K	10.00K	15.00K	10.00K	15.00K
RL	5.00K	7.41K	14.50K	21.80K	16.20K	24.30K
OUT	1.80V	1.81V	1.01V	1.01V	0.97V	0.97V


Cameo Communication INC.

Name: ESX601-54RQ

Size C Document Number Other POWER_02


Date: Tuesday, September 26, 2017 Sheet 5 of 104


Rev 1.0



PMBus Address: 1110001 (bin)
PMBus Address: 71(hex)

Cameo Communication INC.		
Title		
Name:ESX601-54RQ		
Size	Document Number	Rev
A	MAC_POWER_CorePower	1.0
Date:	Tuesday, September 26, 2017	Sheet 6 of 104





PMBus Address: 1110001 (bin)
PMBus Address: 71(hex)

Cameo Communication INC.

Title

Name:ESX601-54RQ

Size
A







Document Number

PHY_POWER

Rev
1.0

Date: Tuesday, September 26, 2017

Sheet 8 of 104



Cameo Communication INC.

Name: ESX601-54RQ

PHY CorePower_Stage

Sheet 9 of 104

