


text for inrush current
option one, connect to charger, ACDRV
option2 without control.
option3 with P-Channel without any control

Minimum input for
charging is set to 1.7.9V
ACDET = 2.4V 817.9V



Default settings
2S 1.5Mhz 1A

default assembly the battery is without NTC
Add comments for assembly of NTC battaery
Temperature Window is
0 to 60 C
10K added for normal operation