




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EVM-089	REV: A	SUN REV: Not in version control
LAYER NAME = Top Overlay			
PLOT NAME = Top Overlay	GENERATED : 5/20/2024	3:32:15 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Top Solder			
PLOT NAME = Top Solder Mask	GENERATED	: 5/20/2024 3:32:16 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Top Layer			
PLOT NAME = Top Layer	GENERATED	: 5/20/2024 3:32:16 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME =		
PLOT NAME = Signal Layer 1	GENERATED : 5/20/2024 3:32:16 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME =		
PLOT NAME = Signal Layer 2	GENERATED : 5/20/2024 3:32:16 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Layer			
PLOT NAME = Bottom Layer	GENERATED	: 5/20/2024 3:32:17 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Solder			
PLOT NAME = Bottom Solder Mask	GENERATED	: 5/20/2024 3:32:17 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EUM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Overlay		
PLOT NAME = Bottom Overlay	GENERATED : 5/20/2024 3:32:17 PM	TEXAS INSTRUMENTS

Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
C	4	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	+/-3.94mil
⌘	283	8.00mil (0.203mm)	PTH	Round	Top Layer - Bottom Layer	
A	42	12.00mil (0.305mm)	PTH	Round	Top Layer - Bottom Layer	
⌘	4	39.37mil (1.000mm)	PTH	Round	Top Layer - Bottom Layer	
▼	5	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	
⌘	2	43.31mil (1.100mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	8	62.99mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	2	137.79mil (3.500mm)	PTH	Round	Top Layer - Bottom Layer	
⌘	2	66.93mil (1.700mm)	PTH	Rectangle	Top Layer - Bottom Layer	
352 Total						

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EUM-D89REV: A	SUN REV: Not in version control
LAYER NAME = Drill Drawing		
PLOT NAME = Drill Drawing	GENERATED : 5/20/2024 3:32:17 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: LMG3100EVM-D89REV: A	SUN REV: Not in version control
LAYER NAME = M2 Board Dimensions		
PLOT NAME = Board Dimensions	GENERATED : 5/20/2024 3:32:18 PM	TEXAS INSTRUMENTS