


Current Point



BLK : 3.1V

VOUT : 58V

LO Point

Not Used

over 0.82A Charging mode

OVP : 60.5V

Not Used

Precharge Mode : If Vout < 39V, Iout = 0.9A

RIGOL

STOP

H

1.00s/

A

2.50MSa/s
Norm

25.00Mpts
400ns/pt

D

-4.48s


T

STOP
RUN

Measure

DH0924S

Waveform View(ROLL)



Result

- Vavg(C1)
-710.66mV
- Vpp(C1)
19.950V
- VRMS(C1)
782.06mV
- Freq(C1)
988.92mHz
- Vmax(C2)
****0ms



1 10.00V/
0.00V

2 200.00mV/
0.00V

3 2.00V/
0.00V

4 50.00mV/
0.00V

D 0 1 2 3
4 5 6 7
8 9 10 11
12 13 14 15

G 5.00V
1.000kHz

M M1 M3
M2 M4



RIGOL

STOP

H

1.00s/

A

2.50MSa/s
Norm

25.00Mpts
400ns/pt

D

-4.48s


T

STOP
RUN

Measure

DH0924S

Waveform View(ROLL)



Result

- Vavg(C1) -710.66mV
- Vpp(C1) 19.950V
- VRMS(C1) 782.06mV
- Freq(C1) 988.92mHz
- Vmax(C2) ****0ms



1 10.00V/
0.00V

2 200.00mV/
0.00V

3 2.00V/
0.00V

4 50.00mV/
0.00V

D 0 1 2 3
4 5 6 7
8 9 10 11
12 13 14 15

G 5.00V
1.000kHz


M M1 M3
M2 M4



P1



P2



P3



P4



P5



P6

