



5

NOTA: Os valores de alguns componentes variam consoante a opção em causa. Confirmar a partir das listas de materiais respectivas.

VIN option	Fuse
dc:19V to 72V	T6.3AH250 (TBC)
dc:38V to 180V	T4AH250 (TBC)
dc:88V to 300V ac:60V to 265V	T2.5AH250 (TBC)

For VIN1: = DNF
For VIN2: = DNF
For VIN3: = FIT



VIN option	R54, R55, R56
dc:19V to 72V	Shunt 2-3
dc:38V to 180V	Shunt 2-3
dc:88V to 300V ac:60V to 265V	Shunt 1-2 + 3-4

Automation Business Unit
Innovation & Development
HW & SW Platforms

Author F. Macedo	Reviewer Diogo C., Majid B.	Approved F. Macedo
Date Thursday, November 06, 2025	Date	Date
Project MAP8510	Document Number AS25003944	Revision 1.0.00
Schematic / MAP8510	Size A3	Sheet 3 of 4
Variant <Core Design>		