


- Horizontal
- Period
- Freq
- Rise Time
- Fall Time
- +Width
- Width



Save

New File

NewFolder


Delete

←

Period 1	Cur:***** Avg:***** Max:***** Min:*****	Freq 1	Cur:***** Avg:***** Max:***** Min:*****	Min 1	Cur:3.18 V Avg:3.19 V Max:3.20 V Min:3.18 V	Max 1	Cur:3.26 V Avg:3.26 V Max:3.28 V Min:3.26 V	Max 2	Cur:15.2mV Avg:13.7mV Max:17.2mV Min:12.0mV
--------------------	--	------------------	--	-----------------	--	-----------------	--	-----------------	--



- Horizontal
- Period
- Freq
- Rise Time
- Fall Time
- +Width
- Width



- Save
- New File
- NewFolder
- Delete

Period 1	Cur: 1.490ms Avg: 1.490ms Max: 1.510ms Min: 1.470ms	Freq 1	Cur: 671 Hz Avg: 671 Hz Max: 680 Hz Min: 662 Hz	Min 1	Cur: 3.44 V Avg: 3.44 V Max: 3.56 V Min: 3.42 V	Max 1	Cur: 3.78 V Avg: 3.79 V Max: 3.94 V Min: 3.78 V	Max 2	Cur: 3.50 V Avg: 3.51 V Max: 3.66 V Min: 3.50 V
--------------------	--	------------------	--	-----------------	--	-----------------	--	-----------------	--





Horizontal



Period



Freq



Rise Time




Fall Time



+Width



-Width



Save

Save

New File

NewFolder

Delete

Period 	Cur: 1.470ms Avg: 1.469ms Max: 1.490ms Min: 1.450ms	Freq 	Cur: 680 Hz Avg: 681 Hz Max: 690 Hz Min: 671 Hz	Min 	Cur: 3.82 V Avg: 3.82 V Max: 3.82 V Min: 3.80 V	Max 	Cur: 4.18 V Avg: 4.18 V Max: 4.18 V Min: 4.16 V	Max 	Cur: 3.86 V Avg: 3.86 V Max: 3.86 V Min: 3.86 V
-------------------	--	-----------------	--	----------------	--	----------------	--	----------------	--

1 = 500mV

2 = 500mV

3 = 10.0mV

4 = 1.00 V

