

# TONGYU TECHNOLOGY LIMITED

## Specification

Customer: \_\_\_\_\_

Part Model : **Lithium Polymer 4770130-6000mAh** \_\_\_\_\_

Part Number: \_\_\_\_\_

Supplier logo: \_\_\_\_\_

Sample Quantity: \_\_\_\_\_

Issue Date: \_\_\_\_\_

Project Name: \_\_\_\_\_

# Content


1.Modified List .....	3
2. Scope .....	4
3. Initial Dimension.....	4
4. Specification .....	5
5. General Performance .....	6
6. Environment Performance .....	6
7. Safe Characteristic .....	7
8.Cautions in use.....	7
9. Battery operation instruction.....	8
10. Other The Chemical Reaction.....	9
11. Period of Warranty .....	9
12. Note .....	9



## 2 .Scope:

This specification describes the basic performance, technical requirement , testing method ,warning and caution of the Li- polymer rechargeable battery .The specification only applies to TONGYU Technology.

## 3. Initial Dimension



H	Max128.0mm	W (	Max70.5mm	T	Max4.7mm
L1	0.5-2.0mm	L2	$8 \pm 1$ mm	L3	$2.5 \pm 1$ mm
W'	$24.5 \pm 1$	d	5mm	$\alpha 1$	$90 \pm 5^\circ$
$\alpha 2$	$90 \pm 5^\circ$				

#### 4.Specification

NO.	Item	Specifications
4.1	Nominal capacity	6000mAh @ 0.2C Discharge
4.2	Nominal voltage	3. 8V
4.3	Charge current	Standard Charge : 0.2C Rapid charge : 0.5C
4.4	Standard Charging method	0.2C CC ( constant current ) charge to 4.35V,then CV(constant voltage 4.35V)charge till charge current decline to $\leq 0.02C$
4.5	Charging time	Standard Charging Approx 3.5 hours Rapid charge Approx 3.5hours
4.6	Max.charge current	Constant Current 0.5C <sub>5</sub> A Constant Voltage 4. 35V 0.02 C <sub>5</sub> A cut-off
4.7	Max.discharge current	Constant current 0.5C <sub>5</sub> A end voltage2.75V
4.8	Standard Discharge Current	Constant current 0.2 C <sub>5</sub> A end voltage2.75V
4.9	Discharge cut-off voltage	2.75V
4.10	Charge cut-off Voltage	4.35V
4.11	Initial Impedance	$\leq 60m\Omega$
4.12	Weight	Approx: 80g
4.13	Operating temperature	Charging: 15°C~45°C Discharging: -10°C~50°C
4.14	Storage temperature	23±5°C
4.15	Storage Humidity	$\leq 75\%$ RH
4.16	Appearance	Without scratch,distortion,contamination and leakage
4.17	Standard environmental condition	Temperature : 23±5°C Humidity : 45-75%RH Atmospheric Pressure : 86-106 Kpa

## 5 General Performance

No.	Item	Test Methods and Condition	Criteria
5.1	0.2C Capacity	After standard charging, laying the battery 5min, then discharging at 0.2C to voltage 2.75V, recording the discharging time.	$\geq 300\text{min}$
5.2	0.5C Capacity	After standard charging, laying the battery 5min, then discharging at 0.5C to voltage 2.75V, recording the discharging time.	$\geq 120\text{min}$
5.3	Cycle Life	Constant current 0.2C charge to 4.35V, then constant voltage charge to current declines to 0.02C, stay 5min, constant current 0.2C discharge to 2.75V, stay 10min. Repeat above steps till continuously discharging capacity Higher than 80% of the Initial Capacities of the Cells	$\geq 500$ times

## 6 Environment Performance

No.	Item	Test Methods and Condition	Criteria
6.1	Discharge at high temperature	After standard charging, laying the Cells 4h at $60 \pm 2^\circ\text{C}$ , then discharging at 1C to voltage 2.75V, recording the discharging time.	$\geq 54\text{min}$
6.2	Discharge at low temperature	After standard charging, laying the Cells 16h at $-20 \pm 2^\circ\text{C}$ , then discharging at 0.2C to voltage 2.5V, recording the discharging time.	$\geq 210\text{min}$
6.3	Capability of keeping electricity	$23 \pm 5^\circ\text{C}$ , After standard charging, laying the battery 28days, discharging at 0.2C to voltage 2.75V, recording the discharging time.	$\geq 240\text{min}$

## 7 Safe Characteristic

No.	Item	Test Methods and Condition	Criteria
7.1	Over charge testing	At $23 \pm 5^\circ\text{C}$ , charging batteries with constant current 3C to voltage 4.6V, then with constant voltage 5V till current decline to 0. Stop test till batteries' temperature $10^\circ\text{C}$ lower than max temperature.	No smoke or fire
7.2	Over discharge	At $23 \pm 5^\circ\text{C}$ , According to the requirements of standard	No fire, no smoke, no

	testing	charge, the battery will be discharged to cut-off voltage, then connect with external load of 30 ohm for 24 hours.	leakage.
7.3	Short-circuit testing	At $23 \pm 5^{\circ}\text{C}$ , After standard charging, connect batteries' anode and cathode by wire which impedance less than $80\text{m}\Omega$ , keep 6h.	No smoke or fire

※ Above testing of safe characteristic must be with protective equipment.

## 8. CAUTIONS IN USE

To ensure proper use of the battery please read the manual carefully before using it. Handling

- Do not expose to, dispose of the battery in fire.
- Do not put the battery in a charger or equipment with wrong terminals connected.
- Avoid shorting the battery
- Avoid excessive physical shock or vibration.
- Do not disassemble or deform the battery.
- Do not immerse in water.
- Do not use the battery mixed with other different make, type, or model batteries.
- Keep out of the reach of children.

. charge and discharge

- Battery must be charged in appropriate charger only.
- Never use a modified or damaged charger.
- Do not leave battery in charger over 24 hours.

. storage

- Store the battery in a cool, dry and well-ventilated area.

. disposal

- Regulations vary for different countries. Dispose of in accordance with local regulations.

## 9. Battery operation instruction

### 9.1 Charging

Charging current: Cannot surpass the biggest charging current which in this specification book stipulated.

Charging voltage: Does not have to surpass the highest amount which in this specification book stipulated to decide the voltage.

Charge temperature: The battery must carry on the charge in the ambient temperature scope which this specification book stipulated.

Uses the constant electric current and the constant voltage way charge, the prohibition reverse charges. If the battery positive electrode and the cathode meet instead, can damage the battery。

## 9.2 Discharging current

The discharging current does not have to surpass this specification book stipulation the biggest discharging current, the oversized electric current electric discharge can cause the battery capacity play to reduce and to cause the battery heat。

## 9.3 discharge temperature

The battery discharge must carry on in the ambient temperature scope which this specification book stipulated

## 9.4 Over-discharges

After the short time excessively discharges charges immediately cannot affect the use, but the long time excessively discharges can cause the battery the performance, battery function losing. The battery long-term has not used, has the possibility to be able to be at because of its automatic flashover characteristic certain excessively discharges the condition, for prevented excessively discharges the occurrence, the battery should maintain the certain electric quantity。

## 9.5 Storing the Batteries

The battery should store in the product specification book stipulation temperature range. If has surpasses above for six months the long time storage, suggested you should carry on additional charge to the battery。

## 10. Period of Warranty

The period of warranty is one year from the date of shipment. TONGYU Technology guarantees to give a replacement in case of cells with defects proven due to manufacturing process instead of the customers abuse and misuse.

## 11. Other The Chemical Reaction

Because batteries utilize a chemical reaction, battery performance will deteriorate over time even if stored for a long period of time without being used. In addition, if the various usage conditions such as charge, discharge, ambient temperature, etc. are not maintained within the specified ranges the life expectancy of the battery may be shortened or the device in which the battery is used may be damaged by electrolyte leakage. If the batteries cannot maintain a charge for long periods of time, even when they are charged correctly, this may indicate it is time to change the battery.

## 12.Note: 备注

Any other items which are not covered in this specification shall be agreed by both parties.