

Termistor 10K - $B(25/85^{\circ}\text{C}) = 3435\text{K}$

[TATEYAMA KAGAKU IND. CO., LTD.]

Temp	Resistance							
	MIN			typ	MAX			
	R:±10%(K)	R:±5%(J)	R:±1%(F)		R:±1%(F)	R:±1%(F)	R:±5%(J)	R:±10%(K)
B:±5%(J)	B:±3%(H)	B:±1%(F)	B:±1%(F)		B:±5%(J)	B:±5%(J)		
-40	164,300.0	184,900.0	205,500.0	214,300.0	223,500.0	264,200.0	276,800.0	
-35	125,200.0	140,000.0	154,600.0	160,800.0	167,200.0	195,200.0	204,500.0	
-30	96,280.0	107,100.0	117,500.0	121,900.0	126,300.0	145,800.0	152,700.0	
-25	74,760.0	82,660.0	90,240.0	93,290.0	96,440.0	110,000.0	115,200.0	
-20	58,560.0	64,390.0	69,910.0	72,080.0	74,300.0	83,840.0	87,830.0	
-15	46,240.0	50,590.0	54,630.0	56,180.0	57,760.0	64,490.0	67,560.0	
-10	36,810.0	40,060.0	43,050.0	44,150.0	45,280.0	50,050.0	52,430.0	
-5	29,510.0	31,970.0	34,180.0	34,980.0	35,780.0	39,170.0	41,030.0	
0	23,830.0	25,690.0	27,350.0	27,910.0	28,490.0	30,900.0	32,370.0	
5	19,380.0	20,790.0	22,030.0	22,440.0	22,850.0	24,560.0	25,730.0	
10	15,850.0	16,940.0	17,870.0	18,160.0	18,460.0	19,660.0	20,600.0	
15	13,050.0	13,890.0	14,590.0	14,790.0	15,000.0	15,850.0	16,600.0	
20	10,810.0	11,450.0	11,980.0	12,130.0	12,270.0	12,860.0	13,470.0	
25	9,000.0	9,500.0	9,900.0	10,000.0	10,100.0	10,500.0	11,000.0	
30	7,393.0	7,833.0	8,194.0	8,293.0	8,392.0	8,791.0	9,209.0	
35	6,108.0	6,496.0	6,820.0	6,914.0	7,010.0	7,397.0	7,749.0	
40	5,074.0	5,415.0	5,706.0	5,795.0	5,886.0	6,255.0	6,553.0	
45	4,237.0	4,538.0	4,798.0	4,882.0	4,967.0	5,315.0	5,568.0	
50	3,557.0	3,822.0	4,055.0	4,132.0	4,211.0	4,537.0	4,753.0	
55	3,000.0	3,234.0	3,442.0	3,514.0	3,587.0	3,889.0	4,074.0	
60	2,543.0	2,750.0	2,936.0	3,002.0	3,068.0	3,348.0	3,508.0	
65	2,165.0	2,348.0	2,515.0	2,575.0	2,636.0	2,894.0	3,032.0	
70	1,851.0	2,014.0	2,163.0	2,218.0	2,274.0	2,512.0	2,631.0	
75	1,589.0	1,734.0	1,868.0	1,918.0	1,970.0	2,188.0	2,292.0	
80	1,370.0	1,499.0	1,619.0	1,665.0	1,713.0	1,913.0	2,004.0	
85	1,186.0	1,301.0	1,409.0	1,451.0	1,494.0	1,678.0	1,758.0	
90	1,031.0	1,134.0	1,231.0	1,269.0	1,309.0	1,478.0	1,548.0	
95	898.7	991.1	1,079.0	1,114.0	1,150.0	1,305.0	1,367.0	
100	786.5	869.5	949.1	981.1	1,014.0	1,157.0	1,212.0	
105	690.7	765.5	837.5	866.9	897.1	1,028.0	1,077.0	
110	608.6	676.1	741.5	768.4	796.1	916.8	960.4	
115	538.0	599.0	658.5	683.2	708.7	819.8	858.9	
120	477.1	532.4	586.6	609.3	632.7	735.3	770.3	
125	424.4	474.6	524.1	544.9	566.5	661.3	692.7	