HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXNL Series (up to 160W)







Power Rating: up to 160 WHeight: 8.6mm to 9.1mm Max

Prootprint: 23.4mm x 21.6mm Max


Frequency Range: 200kHz to 700kHz


@ Isolation (Primary to Secondary): 1500 VDC

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C										
	Turns				Primary ¹	Leakage ²	DCR (mΩ MAX)			Maximum
Part ³				Schematic	Inductance	Inductance				Height
Number	Primary A	Primary B	Secondary		(µMIN)	(µ MAX)	Primary A	Primary B	Secondary	(mm)
PH0801NL	4T	4T	4T (1T:1T:1T:1T)	A1	153	0.45	8.5	8.5	7	8.6
PH0802NL	4T	5T			194	0.45	8.5	12.5	7	8.6
PH0803NL	5T	5T			240	0.55	12.5	12.5	7	8.6
PH0804NL	5T	6T			290	0.60	12.5	14.2	7	9.1
PH0805NL	6T	6T			345	0.65	14.2	14.2	7	9.1
PH0806NL	4T	4T		A2	153	0.45	8.5	8.5	.875 & .875	8.6
PH0807NL	4T	5T	1T & 1T		194	0.55	8.5	12.5	.875 & .875	8.6
PH0808NL	5T	5T			240	0.55	12.5	12.5	.875 & .875	8.6
PH0809NL	5T	6T			290	0.90	12.5	14.2	.875 & .875	9.1
PH0810NL	6T	6T			345	1.00	14.2	14.2	.875 & .875	9.1
PH0811NL	4T	4T	2T & 1T	A3	153	0.45	8.5	8.5	1.75 & 1.75	8.6
PH0812NL	4T	5T			194	0.45	8.5	12.5	1.75 & 1.75	8.6
PHO813NL	5T	5T			240	0.55	12.5	12.5	1.75 & 1.75	9.1
PH0814NL	5T	6T			290	0.65	12.5	14.2	1.75 & 1.75	9.1
PH0815NL	6T	6T			345	0.85	14.2	14.2	1.75 & 1.75	9.1

Mechanicals

PH08XXNL








 Weight
 11.0 grams

 Tape & Reel
 180/reel

 Tray
 40/tray

Unless otherwise specified, all tolerances are ± .010 0 25

Tape & Reel Layout for PH0801NL THRU PH0815NL



NOTE: The above is a universal footprint for a component that has all 11 pins populated. For a given part number, it is only necessary to provide pads for the terminations shown in the schematics on the next page.

HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS





Schematics


PH08XXNL **A2 A3** PH0806 / 07 / 08 / 09 / 10 PHO811 / 12 / 13 / 14 / 15 PH0801 / 02 / 03 / 04 / 05 PRI A PRI A 1T 4 0 4 0 ○ 10 \bigcirc 10 3 0 1T 30 \bigcirc 10 ⊖9 **⊙** 9 PRI B PRI B PRI B 1T 5 0 1T 50 1 0 10 1T PRI AUX PRI AUX PRI AUX (optional) (optional) 1T (optional)

Notes:

- Inductance is measured with both primary windings connected in services (2 to 5, with 3 and 4 shorted).
- 2. Leakage inductance is measured on winding (2-5) with (3-4) and (7, 8, 9, 10, 11) shorted.
- 3. The "NL" suffix indicates an RoHS-compliant part number.
- 4. It is possible to add a primary side aux. winding to any of the above configurations as shown in the schematics. Transformers with primary side aux. winding are non-standard and can be made available upon request. The primary aux. winding can be between 2 and 16 turns. To add a primary aux. winding to a given base, use the

extension .xxx. For example, to add a 4T aux. winding to the base part number PH0801NL, use the part number PH0801.004NL. The height increases by 0.5mm for .xxx part. For example, **PH0801NL** is 8.6mm MAX, **PH0801.004NL** is 9.1mm MAX. 5. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the complete number (i.e. **PH0801.009NL** becomes **PH00801.009NLT**).

6. To determine if the transformer is suitable for your application, it is necessary to ensure that the temperature rise of the component (ambient plus temperature rise) not exceed its operating temperature. To determine the approximate temperature rise of the transformer, refer to the graphs below.




HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXNL Series (up to 160W)



Temperature Rise vs. Power (W) Dissipation



For More Information

101 11101 111101111011110111									
	Pulse Worldwide Headquarters 15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.	Pulse Europe Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany	Pulse China Headquarters Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057	Pulse North China Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China	Pulse South Asia 3 Fraser Street 0428 DUO Tower Singapore 189352	Pulse North Asia 1F, No.111 Xiyuan Road Zhongli District Taoyuan City 32057 Taiwan (R.O.C)			
	Tel: 858 674 8100	Tel: 49 2354 777 100	Tel: 86 755 33966678	Tel: 86 21 62787060	Tel: 65 6287 8998	Tel: 886 3 4356768			
	Fax: 858 674 8262	Fax: 49 2354 777 168	Fax: 86 755 33966700	Fax: 86 2162786973	Fax: 65 6280 0080	Fax: 886 3 4356820			

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.