

# EMI\_Report

## Common Information

Engineer: Youbin.He  
Test Site: AC14  
Power: DC 13.5V  
Environment Conditions: 24 Centigrade,48%RH  
EUT:  
Project NO.:

## Critical\_Freqs

Frequency (MHz)	MaxPeak (dBuV)	Average (dBuV)	Limit (dBuV)	Margin (dB)	Meas. Time (ms)	Bandwidth (kHz)
0.732750	31.28	---	62.00	30.72	---	---
0.732750	---	30.93	42.00	11.07	---	---
0.978000	22.92	---	62.00	39.08	---	---
0.978000	---	22.20	42.00	19.80	---	---
1.466250	---	21.12	42.00	20.88	---	---
1.466250	22.18	---	62.00	39.82	---	---
80.230000	---	24.79	24.00	-0.79	---	---
81.100000	40.22	---	44.00	3.78	---	---

## Common Information

Engineer: Youbin.He  
Test Site: AC14  
Power: DC 13.5V  
Environment Conditions: 24 Centigrade,48%RH  
EUT:  
Project NO.:

