

General Description


The MDU10N070 uses advanced MagnaChip's MOSFET Technology, which provides high performance in on-state resistance, fast switching performance and excellent quality. MDU10N070 is suitable device for Synchronous Rectification For Server and general purpose applications.

Features

- $V_{DS} = 100V$
- $I_D = 53 A @ V_{GS} = 10V$
- $R_{DS(ON)} < 7.0 m\Omega @ V_{GS} = 10V$
 $< 9.1 m\Omega @ V_{GS} = 4.5V$
- 100% UIL Tested
- 100% Rg Tested



PDFN56



Absolute Maximum Ratings ($T_a = 25^\circ C$)

Characteristics		Symbol	Rating	Unit
Drain-Source Voltage		V_{DSS}	100	V
Gate-Source Voltage		V_{GSS}	± 20	V
Continuous Drain Current ⁽¹⁾	$T_C = 25^\circ C$ (Silicon Limited)	I_D	92.2	A
	$T_C = 25^\circ C$ (Package Limited)		53	
	$T_C = 100^\circ C$ (Silicon Limited)		58.3	
	$T_A = 25^\circ C$		19.8	
Pulsed Drain Current ⁽²⁾		I_{DM}	212	
Power Dissipation	$T_C = 25^\circ C$	P_D	119	W
	$T_C = 100^\circ C$		47.6	
	$T_A = 25^\circ C$		5.5	
Single Pulse Avalanche Energy ⁽³⁾		E_{AS}	84.5	mJ
Junction and Storage Temperature Range		T_J, T_{stg}	-55~150	$^\circ C$

Thermal Characteristics

Characteristics	Symbol	Rating	Unit
Thermal Resistance, Junction-to-Ambient ⁽¹⁾	$R_{\theta JA}$	22.7	$^\circ C/W$
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.05	

Ordering Information

Part Number	Temp. Range	Package	Packing	RoHS Status
MDU10N070RH	-55~150°C	PDFN56	Tape & Reel	Halogen Free

Electrical Characteristics (T_J = 25°C)

Characteristics	Symbol	Test Condition	Min	Typ.	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	I _D = 250μA, V _{GS} = 0V	100	-	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	1.2	-	2.2	V
Drain Cut-Off Current	I _{DSS}	V _{DS} = 100V, V _{GS} = 0V	-	-	1.0	μA
Gate Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} = 0V	-	-	±100	nA
Drain-Source ON Resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 20A	-	5.9	7.0	mΩ
		V _{GS} = 4.5V, I _D = 15A	-	7.0	9.1	
Forward Transconductance	g _{fs}	V _{DS} = 10V, I _D = 20A	-	92	-	S
Dynamic Characteristics						
Total Gate Charge	Q _{g(10V)}	V _{DD} = 50V, I _D = 20A, V _{GS} = 10V	-	63	-	nC
Gate-Source Charge	Q _{gs}		-	10	-	
Gate-Drain Charge	Q _{gd}		-	10	-	
Input Capacitance	C _{iss}	V _{DS} = 40V, V _{GS} = 0V, f = 1.0MHz	-	4140	-	pF
Reverse Transfer Capacitance	C _{rss}		-	31	-	
Output Capacitance	C _{oss}		-	586	-	
Turn-On Delay Time	t _{d(on)}	V _{GS} = 10V, V _{DD} = 50V, I _D = 20A, R _G = 3Ω,	-	13.5	-	ns
Rise Time	t _r		-	12	-	
Turn-Off Delay Time	t _{d(off)}		-	61	-	
Fall Time	t _f		-	8.8	-	
Gate Resistance	R _g	f = 1.0 MHz	-	3.0	-	Ω
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V _{SD}	I _S = 20A, V _{GS} = 0V	-	0.8	1.2	V
Body Diode Reverse Recovery Time	t _{rr}	I _F = 20A, dI/dt = 100A/μs	-	TBD	-	ns
Body Diode Reverse Recovery Charge	Q _{rr}		-	TBD	-	nC

Note :

1. Surface mounted FR-4 board by JEDEC (jesd51-7)
2. Pulse width limited by T_{Jmax}
3. E_{AS} is tested at starting T_J = 25°C, L = 1.0mH, I_{AS} = 13A, V_{DD} = 50V, V_{GS} = 10V




Fig.1 On-Region Characteristics




Fig.2 On-Resistance Variation with Drain Current and Gate Voltage




Fig.3 On-Resistance Variation with Temperature




Fig.4 On-Resistance Variation with Gate to Source Voltage




Fig.5 Transfer Characteristics










Fig.6 Body Diode Forward Voltage Variation with Source Current and Temperature





Package Dimension

PDFN56 (5x6mm²)


Dimensions are in millimeters, unless otherwise specified



BACKSIDE VIEW



Land Pattern



Dimension	MILLIMETERS	
	Min	Max
A	0.90	1.10
b	0.33	0.51
C	0.20	0.34
D1	4.50	5.10
D2	-	4.22
E	5.90	6.30
E1	5.50	6.10
E2	-	4.30
e	1.27BSC	
H	0.41	0.71
K	0.20	-
L	0.51	0.71
α	0°	12°

DISCLAIMER:

The Products are not designed for use in hostile environments, including, without limitation, aircraft, nuclear power generation, medical appliances, and devices or systems in which malfunction of any Product can reasonably be expected to result in a personal injury. Seller's customers using or selling Seller's products for use in such applications do so at their own risk and agree to fully defend and indemnify Seller.

MagnaChip reserves the right to change the specifications and circuitry without notice at any time. MagnaChip does not consider responsibility for use of any circuitry other than circuitry entirely included in a MagnaChip product. [MagnaChip](#) is a registered trademark of MagnaChip Semiconductor Ltd.