


# Measurement: Gain / Phase



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	76.47 kHz	1.795 MHz	1.718 MHz
<b>Trace 1</b>	<b>Magnitude (dB)</b>	<b>Magnitude (dB)</b>	<b>Magnitude (dB)</b>
Measurement	0 dB	-29.014 dB	-29.014 dB
<b>Trace 2</b>	<b>Phase (°)</b>	<b>Phase (°)</b>	<b>Phase (°)</b>
Measurement	29.525 °	0 °	-29.525 °

Sweep	
Start frequency:	1 kHz
Stop frequency:	10 MHz
Center frequency:	5 MHz
Span:	9.999 MHz
Sweep mode:	Logarithmic
Numer of points:	401

Hardware setup	
Device type:	Bode100R1
Serial number:	NM092G
Receiver bandwidth:	30 Hz
Output level:	-30 dBm
DUT settling time:	0 ms

Calibration	Full-Range	User-Range
Gain	-	-
Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ
Attenuator setting	Channel 1	Channel 2
Transmission	10 dB	10 dB
Averaging	Compl. Sweeps	Factor
Gain	OFF	10

Comments: