

PA0874NL

4

3

2




1

NOTICE: THE INFORMATION AND DESIGN CONTAINED HEREIN IS THE PROPERTY OF PULSE ELECTRONICS, INC. AND PULSE ELECTRONICS, INC. RESERVES ALL RIGHTS THEREOF.

TEST NOTES:

UNLESS OTHERWISE SPECIFIED, TESTING IS PERFORMED AT 100 KHZ, 100 mV, 25C ±5C.

1. OCL: (100%)  
(2-5) = 243  $\mu$ H ±25%
2. DCR: (100%)  
(2-5) = 37.5 MOHMS MAXIMUM  
(1-6) = 475 MOHMS MAXIMUM  
(8-10) = 1.75 MOHMS MAXIMUM  
(7-11) = 400 MOHMS MAXIMUM
3. HIPOT: (100%) 1750 VDC FOR 6 SECONDS BETWEEN PINS (2-7,8), (3-7,8)  
CURRENT LIMITED TO LESS THAN 100  $\mu$ A
4. LEAKAGE: (100%)  
(2-5) AND (7,8,9,10,11)  
SHORTED = .45  $\mu$ H MAXIMUM



UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES. TOLERANCES ARE: .01 ANGLES ± 1° .005 SCALE NONE DWG. NO. PA0876.003NL REV. SO

DO NOT SCALE DRAWING

SIZE B01961

SCALE NONE

CADD FILE

PA0876NL-9

SHEET 9 OF 9