



EEPROM



四线制



触发器








Table 8-1. Function table



INPUTS				OUTPUTS	
PRE	CLR	CLK	D	Q	$\bar{Q}$
L	H	X	X	H	L
H	L	X	X	L	H
L	L	X	X	H ⁽¹⁾	H ⁽¹⁾
H	H	↑	H	H	L
H	H	↑	L	L	H
H	H	L	X	Q ₀	$\bar{Q}_0$

(1) This configuration is nonstable; that is, it does not persist when PRE or CLR returns to its inactive (high) level.

Title		
Size	Number	Revision
A3		
Date:	2021-12-07	Sheet of
File:	C:\Users\...PWR_CURRENT_V0.1.SchDoc	Drawn By:



OPT设置对应于4相或3相操作的同步输出信号的相位滞后
nFAULT 故障标志 输出低表示故障
IOUT1 CH-1电感器电流监测器引脚
SYNCOUT 时钟输出
IOUT2 CH-2电感器电流监测器引脚
FB 模拟电流控制
SYNCIN 时钟输入
UVLO <1.25V 静态电流关闭模式
<1.25V UVLO <2.5V 初始化
>2.5V 进入故障自锁后开始工作
OVPB LV端过压保护
OVPA HV端过压保护
DIR 充放电开关切换 DIR>2V 充电模式 <1V放电模式
EN1 通道1使能 >2.4V
EN2 通道2使能 >2.4V



Title		
Size	Number	Revision
A3		
Date:	2021-12-07	Sheet of
File:	C:\Users\...PWR LM5170_V0.1.SchDoc	Drawn By: