


**PRODUCT SUMMARY**

	$V_{(BR)DSS}$	$R_{DS(ON)}$	$I_D$
Q2	30V	4.9mΩ	64A
Q1	30V	7.8mΩ	40A



1 : G1  
2,3,4 : D1  
5,6,7 : S2  
8 : G2  
9 : S1/D2

**ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = 25 °C Unless Otherwise Noted)**

PARAMETERS/TEST CONDITIONS		SYMBOL	Q2	Q1	UNITS
Drain-Source Voltage		$V_{DS}$	30	30	V
Gate-Source Voltage		$V_{GS}$	±20	±20	V
Continuous Drain Current <sup>3</sup>	T <sub>C</sub> = 25 °C	$I_D$	64	40	A
	T <sub>C</sub> = 100 °C		40	25	
Pulsed Drain Current <sup>1</sup>		$I_{DM}$	150	90	
Continuous Drain Current	T <sub>A</sub> = 25 °C	$I_D$	21	14	
	T <sub>A</sub> = 70 °C		17	11	
Avalanche Current		$I_{AS}$	35	21	
Avalanche Energy	L = 0.1mH	$E_{AS}$	61	22	mJ
Power Dissipation	T <sub>C</sub> = 25 °C	$P_D$	37	24	W
	T <sub>C</sub> = 100 °C		15	9.6	
Power Dissipation <sup>4</sup>	T <sub>A</sub> = 25 °C	$P_D$	4	3.1	W
	T <sub>A</sub> = 70 °C		2.6	2	
Operating Junction & Storage Temperature Range		T <sub>j</sub> , T <sub>stg</sub>	-55 to 150		°C

**THERMAL RESISTANCE RATINGS**

THERMAL RESISTANCE		SYMBOL	TYPICAL	MAXIMUM	UNITS
Junction-to-Ambient <sup>2</sup>	t ≤ 10s	Q2		30	°C / W
		Q1		40	
	Steady-State	Q2		56	
		Q1		72	
Junction-to-Case		R <sub>θJC</sub>	Q2	3.3	
		R <sub>θJC</sub>	Q1	5.2	

<sup>1</sup>Pulse width limited by maximum junction temperature T<sub>J(MAX)</sub>=150°C.

<sup>2</sup>The value of R<sub>θJA</sub> is measured with the device mounted on 1in<sup>2</sup> FR-4 board with 2oz. Copper, in a still air environment with T<sub>A</sub> =25°C. The value in any given application depends on the user's specific board design.

<sup>3</sup>Package limitation current :Q1=25A,Q2=25A

<sup>4</sup>The Power dissipation is based on R<sub>θJA</sub> t ≤ 10s value.

**ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25 °C, Unless Otherwise Noted)**

PARAMETER	SYMBOL	TEST CONDITIONS	LIMITS			UNIT	
			MIN	TYP	MAX		
<b>STATIC</b>							
Drain-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	V <sub>GS</sub> = 0V, I <sub>D</sub> = 1mA	Q2	30		V	
		V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA	Q1	30			
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	Q2	1.3	1.6	2.3	
			Q1	1.27	1.36	2.3	
Gate-Body Leakage	I <sub>GSS</sub>	V <sub>DS</sub> = 0V, V <sub>GS</sub> = ±20V	Q2			±100	
			Q1			±100	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> = 24V, V <sub>GS</sub> = 0V	Q2			0.5	
			Q1			1	
		V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0V, T <sub>J</sub> = 55 °C	Q2			5	
			Q1			10	
Drain-Source On-State Resistance <sup>1</sup>	R <sub>DS(ON)</sub>	V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 16A	Q2		3.4	5.1	
			Q1		6.8	11	
			Q2		2.7	4.9	
			Q1		5.3	7.8	
Forward Transconductance <sup>1</sup>	g <sub>fs</sub>	V <sub>DS</sub> = 5V, I <sub>D</sub> = 20A	Q2		70	S	
		V <sub>DS</sub> = 5V, I <sub>D</sub> = 11A	Q1		66		
<b>DYNAMIC</b>							
Input Capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0V, V <sub>DS</sub> = 15V, f = 1MHz	Q2		2148	pF	
			Q1		853		
Output Capacitance	C <sub>oss</sub>		Q2		402	pF	
			Q1		149		
Reverse Transfer Capacitance	C <sub>rss</sub>		Q2		255	pF	
			Q1		109		
Gate Resistance	R <sub>g</sub>	V <sub>GS</sub> = 0V, V <sub>DS</sub> = 0V, f = 1MHz	Q2		1.6	Ω	
			Q1		0.8		
Total Gate Charge <sup>2</sup>	Q <sub>g</sub>	Q2 V <sub>DS</sub> = 15V, V <sub>GS</sub> = 10V, I <sub>D</sub> = 20A Q1 V <sub>DS</sub> = 15V, V <sub>GS</sub> = 10V, I <sub>D</sub> = 11A	V <sub>GS</sub> = 10V	Q2		44	nC
			V <sub>GS</sub> = 4.5V	Q1		18	
				Q2		23.3	
			Gate-Source Charge <sup>2</sup>	Q <sub>gs</sub>	Q1		
Q2					5.4		
Gate-Drain Charge <sup>2</sup>	Q <sub>gd</sub>		Q1		2.1		
			Q2		11		
				Q1		4.8	

Turn-On Delay Time <sup>2</sup>	$t_{d(on)}$	Q2 $V_{DS} = 15V$ , $I_D \cong 20A, V_{GS} = 10V, R_{GEN} = 6\Omega$ Q1 $V_{DS} = 15V$ , $I_D \cong 11A, V_{GS} = 10V, R_{GEN} = 6\Omega$	Q2		30		nS
Rise Time <sup>2</sup>	$t_r$		Q1		25		
Turn-Off Delay Time <sup>2</sup>	$t_{d(off)}$		Q2		20		
			Q1		21		
Fall Time <sup>2</sup>	$t_f$		Q2		61		
			Q1		40		
		Q2		22			
		Q1		20			
<b>SOURCE-DRAIN DIODE RATINGS AND CHARACTERISTICS (<math>T_J = 25^\circ C</math>)</b>							
Continuous Current <sup>3</sup>	$I_S$		Q2			37	A
			Q1			20	
Forward Voltage <sup>1</sup>	$V_{SD}$	$I_F = 20A, V_{GS} = 0V$	Q2			1	V
		$I_F = 11A, V_{GS} = 0V$	Q1			1.2	
Reverse Recovery Time	$t_{rr}$	Q2	Q2		21		nS
		$I_F = 20A, dl_F/dt = 100A / \mu S$	Q1		13.5		
Reverse Recovery Charge	$Q_{rr}$	Q1	Q2		6.5		nC
		$I_F = 11A, dl_F/dt = 100A / \mu S$	Q1		4		

<sup>1</sup>Pulse test : Pulse Width  $\leq 300 \mu sec$ , Duty Cycle  $\leq 2\%$ .


<sup>2</sup>Independent of operating temperature.

<sup>3</sup>Package limitation current : Q1=25A, Q2=25A


**TYPICAL PERFORMANCE CHARACTERISTICS**

**Q2**


**Output Characteristics**




**Transfer Characteristics**




**Gate charge Characteristics**




**Capacitance Characteristic**




**On-Resistance VS Gate-To-Source**




**On-Resistance VS Drain Current**




**On-Resistance VS Temperature**




**Source-Drain Diode Forward Voltage**




**Safe Operating Area**



**Single Pulse Maximum Power Dissipation**




**Transient Thermal Response Curve**




**Q1**


**Output Characteristics**




**Transfer Characteristics**




**Gate charge Characteristics**




**Capacitance Characteristic**




**On-Resistance VS Gate-To-Source**




**On-Resistance VS Drain Current**




**On-Resistance VS Temperature**




**Source-Drain Diode Forward Voltage**



**Safe Operating Area**



**Single Pulse Maximum Power Dissipation**



**Transient Thermal Response Curve**

