







[illegible]



PQ3220S	C1(mm ⁻¹)	0.326
PQ	Le(mm)	55.5
A 32.00 ±0.50	Ae(mm ²)	170.0
B 20.55 ±0.25	Amin(mm ²)	142.1
C 22.00 ±0.50	Ve(mm ³)	9420
D1 27.50 ±0.50	Vmin(mm ³)	7885
D2 19.00 min.	Ac(mm ²)	142.0
E 13.45 ±0.25	Aw(mm ²)	80.8
F 11.50 ±0.30	W(g/set)	42

AL value **PL-7**
5000

AL value
- Unit : nH/N²
- Measuring conditions : 1kHz, 0.1V, 23°C
- Tolerance : ±25%
- SM-100 : Non mirror grinding



VER	UP DATE	DATE	SIGN	DATE	13,08,2020	Firma/Manufacturer	Bilgilendirme/Information	Stok No/Stock No	Müşteri/Customer	
				DRW	ALİ AKCAN		PQ 32/20	SM 32202034		Sayfa
				APPR			SMPS TRAFOSU			Page
										2