



| | Cursor 1 | Cursor 2 | Delta C2-C1 |
|-------------|----------------|----------------|----------------|
| Frequency | 1 MHz | 10 MHz | 9 MHz |
| Trace 1 | Magnitude (dB) | Magnitude (dB) | Magnitude (dB) |
| Measurement | 53.548 dB | 15.413 dB | -38.136 dB |

| Sweep | |
|-------------------|-------------|
| Start frequency: | 10 Hz |
| Stop frequency: | 10 MHz |
| Center frequency: | 5 MHz |
| Span: | 10 MHz |
| Sweep mode: | Logarithmic |
| Numer of points: | 201 |

| Hardware setup | |
|---------------------|-----------|
| Device type: | Bode100R2 |
| Serial number: | PC200H |
| Receiver bandwidth: | 30 Hz |
| Output level: | 100 mVpp |
| DUT settling time: | 100 ms |

| Calibration | Full-Range | User-Range |
|-------------|------------|------------|
| Gain | - | - |

| Termination | Channel 1 | Channel 2 |
|-------------|--------------|-------------|
| Gain | 1 M Ω | 50 Ω |

| Attenuator setting | Channel 1 | Channel 2 |
|--------------------|-----------|-----------|
| Transmission | 20 dB | 20 dB |