



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	464.159 Hz	21.544 kHz	21.08 kHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	63.739 dB	26.985 dB	-36.754 dB

Sweep	
Start frequency:	10 Hz
Stop frequency:	10 MHz
Center frequency:	5 MHz
Span:	10 MHz
Sweep mode:	Logarithmic
Numer of points:	401

Hardware setup	
Device type:	Bode100R1
Serial number:	LM498C
Receiver bandwidth:	30 Hz
Output level:	100 mVpp
DUT settling time:	100 ms

Calibration	Full-Range	User-Range
Gain	Active	-
Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ
Attenuator setting	Channel 1	Channel 2
Transmission	10 dB	10 dB