


Lab Notebook Entry from LeCroy DSO
DSO S/N: LCRY0604P14011
User: LeCroyUser
Time: 6/1/2002 1:17:59 AM

TI 40210



No filter on ISNS



Channel Status

	C2	C3	C4
V / Div	2.00 V	100 V	500 mV
Offset	-5.100 V	-35.0 V	-70 mV
Coupling	DC1MΩ	DC1MΩ	DC1MΩ
BW-Limit	Full	Full	Full
Probe	10	10	10
Sweeps	---	---	---


Acquisition Status

Time / Div 50.0 ms Sampling Rate 5.0 MS/s

Horizontal	Time / Pt	200.000 ns	Sampling Mode	RealTime
	Pts / Div	250.0000 kS	Trigger Delay	-16 ms
	Mode	Stop	Slope	Positive
Trigger	Type	Edge	Level	2.52 V
	Source	C2	Coupling	DC

Lab Notebook Entry from LeCroy DSO
DSO S/N: LCRY0604P14011
User: LeCroyUser
Time: 6/1/2002 2:24:55 AM

TI TPS40210 power up



Channel Status

	C2	C3	C4
V / Div	2.00 V	100 V	500 mV
Offset	-5.100 V	-35.0 V	-70 mV
Coupling	DC1M Ω	DC1M Ω	DC1M Ω

Vertical	<i>BW-Limit</i>	Full	Full	Full
	<i>Probe</i>	10	10	10
	<i>Sweeps</i>	---	---	---

Acquisition Status

Horizontal	<i>Time / Div</i>	100 ms	<i>Sampling Rate</i>	2.5 MS/s
	<i>Time / Pt</i>	400.000 ns	<i>Sampling Mode</i>	RealTime
	<i>Pts / Div</i>	250.0000 kS	<i>Trigger Delay</i>	-398 ms
Trigger	<i>Mode</i>	Stop	<i>Slope</i>	Positive
	<i>Type</i>	Edge	<i>Level</i>	2.52 V
	<i>Source</i>	C2	<i>Coupling</i>	DC