

RoHS Compliant Product
A suffix of "-C" specifies halogen & lead-free

DESCRIPTION


The SPR80N10S-C is the highest performance N-ch MOSFETs with extreme high cell density , which provide excellent $R_{DS(ON)}$ and gate charge for most of the synchronous buck converter applications .

The SPR80N10S-C meet the RoHS and Green Product Requirement with full function reliability approved.

FEATURES

- High Speed Power Switching
- Green Device Available
- Super Low Gate Charge

MARKING



PACKAGE INFORMATION

Package	MPQ	Leader Size
PR-8PP	3K	13 inch


ORDER INFORMATION

Part Number	Type
SPR80N10S-C	Lead (Pb)-free and Halogen-free


ABSOLUTE MAXIMUM RATINGS (T_A=25°C unless otherwise specified)

Parameter		Symbol	Rating	Unit
Drain-Source Voltage		V _{DS}	100	V
Gate-Source Voltage		V _{GS}	±20	V
Continuous Drain Current ¹ @V _{GS} =10V	T _C =25°C	I _D	80	A
	T _C =70°C		61	A
Pulsed Drain Current ²		I _{DM}	140	A
Total Power Dissipation ³	T _C =25°C	P _D	108	W
Operating Junction & Storage Temperature		T _J , T _{STG}	-55~150	°C
Thermal Data				
Thermal Resistance Junction-Ambient ¹	t≤10sec	R _{θJA}	25	°C / W
	Steady State		55	°C / W
Thermal Resistance Junction-Case ¹		R _{θJC}	1.15	°C / W

PR-8PP



REF.	Millimeter		REF.	Millimeter	
	Min.	Max.		Min.	Max.
A	4.9	5.1	G	0.8	1.0
B	5.7	5.9	H	0.254	Ref.
C	5.95	6.2	I	4.0	Ref.
D	1.27	BSC.	J	3.4	Ref.
E	0.35	0.49	K	0.6	Ref.
F	0.1	0.2	L	1.4	Ref.









ELECTRICAL CHARACTERISTICS ($T_J=25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions
Drain-Source Breakdown Voltage	BV_{DSS}	100	-	-	V	$V_{GS}=0$, $I_D=250\mu A$
Gate-Threshold Voltage	$V_{GS(th)}$	1	-	2.5	V	$V_{DS}=V_{GS}$, $I_D=250\mu A$
Forward Transfer conductance	g_{fs}	-	85	-	S	$V_{DS}=5V$, $I_D=20A$
Gate-Source Leakage Current	I_{GSS}	-	-	± 100	nA	$V_{GS}= \pm 20V$
Drain-Source Leakage Current	I_{DSS}	-	-	1	μA	$V_{DS}=80V$, $V_{GS}=0$, $T_J=25^{\circ}C$
		-	-	5		$V_{DS}=80V$, $V_{GS}=0$, $T_J=55^{\circ}C$
Static Drain-Source On-Resistance ²	$R_{DS(ON)}$	-	6.6	8.5	m Ω	$V_{GS}=10V$, $I_D=13.5A$
		-	8.7	10.5		$V_{GS}=4.5V$, $I_D=11.5A$
Total Gate Charge	Q_g	-	45	-	nC	$I_D=13.5A$ $V_{DS}=50V$ $V_{GS}=10V$
Gate-Source Charge	Q_{gs}	-	9.5	-		
Gate-Drain (“Miller”) Change	Q_{gd}	-	4.8	-		
Turn-on Delay Time	$T_{d(on)}$	-	10	-	nS	$V_{DD}=50V$ $I_D=13.5A$ $V_{GS}=10V$ $R_G=3\Omega$
Rise Time	T_r	-	6.5	-		
Turn-off Delay Time	$T_{d(off)}$	-	45	-		
Fall Time	T_f	-	7.5	-		
Input Capacitance	C_{iss}	-	3320	-	pF	$V_{GS}=0$ $V_{DS}=50V$ $f=1.0MHz$
Output Capacitance	C_{oss}	-	605	-		
Reverse Transfer Capacitance	C_{rss}	-	20	-		
Source-Drain Diode						
Diode Forward Voltage ²	V_{SD}	-	-	1.2	V	$I_S=1A$, $V_{GS}=0V$
Continuous Source Current ¹	I_S	-	-	80	A	$V_G=V_D=0$, Force Current
Reverse Recovery Time	t_{rr}	-	33	-	nS	$I_F=13.5A$, $dI/dt=100A/\mu s$, $T_J=25^{\circ}C$
Reverse Recovery Charge	Q_{rr}	-	150	-	nC	

Notes:

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$.
3. The power dissipation is limited by 150°C junction temperature.

CHARACTERISTIC CURVES



CHARACTERISTIC CURVES




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform




Fig.11 Unclamped Inductive Switching Waveform