

## Texas Instruments Qualification Summary

Quality and reliability are built into TI's culture, with the goal of providing customers high quality products. TI's semiconductor technologies are developed with a minimum goal of fewer than 50 Failures in Time (FIT) at 100,000 Power-On-Hours at 105C junction temperature. TI builds simulations, accelerated testing, and robustness evaluations into the product development process. During the product development process, TI carefully assesses silicon process reliability, package reliability, and silicon/package interaction.

TI also evaluates manufacturability of the device to verify a robust silicon and assembly flow to enable continuity of supply to customers. Non-Automotive devices are qualified with industry standard test methodologies performed primarily to the intent of the Joint Electron Devices Engineering Council (JEDEC). TI qualifies new devices, significant changes, and product families based on JEDEC JESD47. The data shown is representative of the material sets, processes, and manufacturing sites used by the device family.

### **Important information/disclaimer**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

## Texas Instruments Qualification Summary

<b>Qualification summary for:</b>	<b>TLV62585PDRLR</b>
<b>Report date:</b>	<b>11/17/2022</b>

Stress	Reference	Min lot qty	SS / lot	Condition	Duration	Result
HTOL	JESD22-A108	3	77	Life test, 125C	1000 hours	Pass
HTSL	JESD22-A103	3	25	High temp storage ba ke 150C	1000 hours	Pass
AC/UHAST	JESD22-A102/JESD2 2-A118	3	25	Autoclave 121C or un biased HAST 130C / 8 5% RH	96 hours	Pass
THB/HAST	JESD22-A101/JESD2 2-A110	3	25	THB 85C/85%RH or H AST 130C/110C/85% RH	1000 hours or 96 hou rs	Pass
TC	JESD22-A104	3	25	Temperature cycle -6 5/150C	500 cycles	Pass
SD	J-STD-002	3	22	Per specification	>95% lead coverage	Pass
HBM	JS-001	1	3	ESD - HBM	Classification	<a href="#">See data sheet</a>

### Important information/disclaimer

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI reference number:10005991

Stress	Reference	Min lot qty	SS / lot	Condition	Duration	Result
CDM	JESD22-C101	1	3	ESD - CDM	Classification	<a href="#">See data sheet</a>
LU	JESD78	1	3	Latch-up	Per JESD78	Pass
MSL	J-STD-020	—	—	Per J-STD-020	Classification	<a href="#">See data sheet</a>

**Important information/disclaimer**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI’s products are provided subject to [TI’s Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI’s provision of these resources does not expand or otherwise alter TI’s applicable warranties or warranty disclaimers for TI products.

TI reference number:10005991