

# ***Simple Guide to CEDV Data Collection for Gauging Parameter Calculator (GPC)***

---

---

---

## **1 Tool Summary**

Gauging Parameter Calculator (GPC) is a math calculation and simulation tool that helps the battery designer to obtain matching Compensated End of Discharge Voltage (CEDV) coefficients for the specific battery profile. The tool allows the user to increase the accuracy of the fuel gauge IC over temperature.

The battery pack must use one of TI's CEDV algorithm-based fuel gauges. It accepts 3 pairs of log files that can be created with various user equipment or by using TI's Battery Management Studio (bqStudio) software with a CEDV evaluation board connected through USB.

This guide describes how to obtain the 3 pairs of log files without the use of a TI EVM or TI bqStudio software.

## **2 Required Data**

The GPC tool requires a single .zip file containing seven text files as its input. The name of the .zip file is not important. Six of the files are data logs and the other is a configuration file describing various aspects of the battery pack.

### **2.1 Configuration File (1 ea)**

The configuration file is a text file named config.txt and is an ASCII text dictionary containing the following information:

- NumCellSeries = <number series cells>
- CellTermV = <cell termination voltage expressed as an unsigned decimal value>
- ChemType = <1 is LiCoO2(default), 2 is NiMH, 3 is Lead-Acid, 4 is LiFePO4, 5 is Lithium Titanate>
- VoltageColumn = <Zero based column number for the voltage data in your data logs>
- CurrentColumn = <Zero based column number for the current data in your data logs>
- TemperatureColumn = <Zero based column number for the temperature data in your data logs>
- ElapsedTimeColumn = <Zero based column number for the elapsed time data in your data logs>
- FitMaxSOC% = <Integer ranging from 8 to 14. Typical is 12>
- FitMinSOC% = <Integer ranging from 2 to 6. Typical is 6>
- LearnSOC% = <Integer ranging from 5 to 12. Typical is 7>

## 2.2 Data Log Files (6 ea)

- Continuous discharge at 2 different rates, from fully charged state until termination voltage is reached.
- Time (in seconds elapsed), Voltage (in millivolts), current (in milliamps where discharge current is negative), and direct cell temperature (in degrees Celsius, one decimal place is acceptable) are recorded and stored as separate columns separated by commas. Data files must be saved as .csv. Any text should be removed from files prior to submission.
- An easy recording method utilizes TI's bqStudio software utility called GPC Packager that reads data directly from a TI fuel-gauge.
- Make sure to set overtemperature limits in the fuel-gauge higher than the expected cell temperature during the test.
- The first rate should be average typical, and second should be average high for your application. Note that high rate should **not** be maximum peak current, but rather maximum average sustained rate that can practically occur in the application.
- Discharge does not have to be constant current, it can be any load pattern typical for your application, including constant power. It is OK to have zero current rows before and after the discharge.
- The size of each discharge log must not exceed 2MB.
- Fully charge the battery prior to application of the test pattern.
- Test at both rates has to be performed at 3 different temperatures. Typical temperatures for the test are 5°C, 30°C, 50°C. Note that cells heat-up during high rate discharge, so, if your maximum spec temperature is 70°C, you might use a chamber temperature of 50°C. See additional explanation on temperatures in [Section 2.2.1](#).
- As result of all tests, 6 files are obtained.
- If the temperature was changed, the battery should reach thermal equilibrium for at least 2 hours prior to testing.

The GPC tool requires six continuous discharge logs as inputs. These are most easily thought of as being three pairs of files with each pair at a specific cell temperature. The ASCII format is very flexible and simple, and the columns can be in any order since the column positions are defined in the config.txt file.

Each of the files represents a separate discharge run of your battery pack at a given temperature and with a given load. Precision of the measurements is important in all aspects. The following names are given to the six distinct discharge logs:

hightemp\_highrate.csv  
hightemp\_lowrate.csv

roomtemp\_highrate.csv  
roomtemp\_lowrate.csv

lowtemp\_highrate.csv  
lowtemp\_lowrate.csv

### 2.2.1 Temperature Parameters

The low temperature value is typically 0°C or 5°C but the correct value to use for that pair of logs is the expected low cell temperature limit in your application before the load is applied. Naturally, as you begin the discharge log there is some self-heating of the cells, this is part of what the log tracks.

The nominal temperature value is typically 25°C or 30°C but most importantly should be placed approximately in the center of the high and low temperature extremes. The exact value is not critical.

The high temperature value is typically 40°C or 50°C, but the correct value to use for that pair of logs is the expected high cell temperature limit in your application before the load is applied.

If the temperature was changed, the battery should be soaked at the new desired temperature for 2 hours prior to starting the discharge.

### 2.2.2 Example Config.txt File

```
NumCellSeries=6  
CellTermV=3000  
ChemType=1  
VoltageColumn=1  
CurrentColumn=3  
TemperatureColumn=2  
ElapsedTimeColumn=0  
FitMaxSOC%=12  
FitMinSOC%=6  
LearnSOC%=7
```

### 2.2.3 Excerpted Example Data Log

In this excerpt, the columns are:

elapsed time, voltage, temperature, and current.

```
92, 25509, 50.9, 0  
96, 25504, 50.9, 0  
100, 25065, 50.9, -10102  
104, 25019, 51, -10104
```

## Revision History

Changes from Original (October 2014) to A Revision	Page
• Changed ChemTypes for 2, 3, 4, and 5 to NiMH, Lead-Acid, LiFePO <sub>4</sub> , and Lithium Titanate, respectively .....	<a href="#">1</a>

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Applications Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)