

Our PCB (CCM) New Circuit - Vin 48V, Vout 5V, Load Current 100mA

R40 = 400k (switching freq = 250k)

R38 = 715

R42 = 196k

C25 = .91nF

C27//C30 = .560nF

C29 = .010nF

PH



Vout


Sometimes looks like this



And sometimes like this



Comp




Our PCB (CCM) Original Circuit

As described in schematic

PH



Vout



Comp

