

load current	Read(8Ch)		1	2	3	4	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	hex	dec	N	bin	hex	Y	read value
0.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
0.001 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
0.010 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
0.100 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
1.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
2.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
3.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
4.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
5.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
6.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
7.000 A	0x00b8	b800	1011	1000	0000	0000	1	0	1	1	1	0	0	0	0	0	0	0	0	0	0	0	17	23	-9	000000000000	0 0 0	0	0.00 A
8.000 A	0x4ab1	b14a	1011	0001	0100	1010	1	0	1	1	0	0	0	1	0	1	0	0	1	0	1	0	16	22	-10	00101001010	1 4 A	330	0.32 A
9.000 A	0xdebb	bbde	1011	1011	1101	1110	1	0	1	1	1	0	1	1	1	1	0	1	1	1	1	0	17	23	-9	01111011110	3 D E	990	1.93 A
10.000 A	0x41c2	c241	1100	0010	0100	0001	1	1	0	0	0	0	1	0	0	1	0	0	0	0	0	1	18	24	-8	01001000001	2 4 1	577	2.25 A
12.000 A	0x6aca	ca6a	1100	1010	0110	1010	1	1	0	0	1	0	1	0	0	1	1	0	1	0	1	0	19	25	-7	01001101010	2 6 A	618	4.83 A
30.000 A			0000	0000	0000	0000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	00	0	0	000000000000	0 0 0	0	0.00 A
40.000 A			0000	0000	0000	0000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	00	0	0	000000000000	0 0 0	0	0.00 A
50.000 A			0000	0000	0000	0000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	00	0	0	000000000000	0 0 0	0	0.00 A
60.000 A			0000	0000	0000	0000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	00	0	0	000000000000	0 0 0	0	0.00 A

IMON_Pin				
load current	VIMON	Io (Calculated value)	read value	Δ
0 A	2.0 mV	0.38A	0A	0.38A
6 A	2.6 mV	0.49A	0A	0.49A
7 A	2.6 mV	0.49A	0A	0.49A
8 A	8.0 mV	1.51A	0.32A	1.19A
10 A	18.0 mV	3.40A	2.25A	1.14A
12 A	27.0 mV	5.09A	4.83A	0.27A